

FACIT to Blind Test

FACIT TO BLIND TEST LED TEST OSLO 30 AUGUST 2016

How to connect a fixture with a file name :

The SCENE number is linked to a fixture, in one of the four setups. The Fixture do not have have one number, but 4.

As an example comparing HALOGEN between BB&S and DMG ,open the files with SCENE

Numbers 9 , 23 and 29 where 9 is the reference source, 23 stands for DMG SL1 and 29 the BB&S in Halogen setup.

TESTING FIXTURE	SCENE	CLOSE UP	WIDE SHOT	Take 2 filename
NATURAL DAYLIGHT (WINDOW)	1	1 CLOSE 1C002	1 WIDE 1C001	
HMI (Arrisun 5)	8	8 CLOSE 1C016	8 WIDE 1C015	
HALOGEN 2 Kw (Blonde)	9	9 CLOSE 1C018	9 WIDE 1C017	
CANDLE LIGHTS	10	CLOSE TAKE 1 1C020	10 WIDE 1C019	10 CANDLE CLOSE TAKE 2 1C021

SOFTLIGHTS JULIETTE bicolor				
Nat. Daylight + Softlights Juliette	2	2 CLOSE 1C004	2 WIDE 1C003	
Softlights Juliette for Daylight	18	18CLOSE 2C002	18 WIDE 2C001	
Softlights Juliette for Halogen	19	19 CLOSE 2C004	19 WIDE 2C003	
Softlights Juliette for Candle	12	12 CLOSE 1C025	12 WIDE 1C024	

WESTCOTT FLEX				
Natural Daylight + Westcott		NO DATA		
Westcott for Daylight	30	30 CLOSE 2C026	30 WIDE 2C025	
Westcott for Halogen	31	31 CLOSE 2C028	31 WIDE 2C027	
Westcott for Candle	11	A001C023	A001C022	

ARRI-SKYPANEL				
Nat. Daylight + SKY P.	3	A001C006	A001C005 MISSING	
Daylight	20	A002C006	A002C005	
Halogen	21	A002C008	A002C007	
Candle	15	A001C032	A001C031	

DMG- SL1				
Nat. Daylight + DMG	4	A001C008	A001C007	
Daylight	22	A002C010	A002C009	
Halogen	23	A002C012	A002C011	
Candle	13	A001C0027	A001C0026	

FACIT to Blind Test

BB&S-AREASOFT 48			
Nat. Daylight + Areasoft 48	7	A001C014	A001C013
Daylight	28	A002C022 MISSING	A002C021
Halogen	29	A002C024	A002C023 MISSING
Candle	17	A001C036	A001C035

KINOFLO SELECT LED 30			
Nat. Daylight + KINOFLO	5	A001C010	A001C009
Daylight	24	A002C014	A002C013
Halogen	25	A002C016	A002C015
Candle	14	A001C030	A001C028

Wide take 2: A001C029

THE LIGHT/VELVET			
Nat. Daylight + VELVET	6	A001C012	A001C011
Daylight	26	A002C018	A002C017
Halogen	27	A002C020	A002C019
Candle	16	A001C034	A001C033

FILLEX- Q1000			
Daylight	32	A002C030	A002C029
Halogen	33	A002C032	A002C031